

POWER PROFILE #6

BORCOS FIRDAUS I



VESSEL SPECIFICATIONS

Application: Crewboat
Operating Location: Miri, Sarawak, E. Malaysia
Length: 40.25 m
Beam: 7.5 m
Main Engines: 2x KTA38-M2, 1x KTA50-M2
Generator Sets: 6BT generators
New Build

ENGINE SPECIFICATIONS

KTA50-M2

Power: 1343 kW (1800 BHP) @ 1900 RPM
Rating: Heavy Duty
Configuration: V-16 cylinder, 4 stroke

KTA38-M2

Power: 1007 kW (1350 BHP) @ 1950 RPM
Rating: Heavy Duty
Configuration: V-12 cylinder, 4 stroke
Fuel Consumption*: 174.0 L/hr (46.0 gal/hr)

6BT Generator Set

Power: 68 kWe @ 50 Hz, 415 volt
Rating: Prime Power

* ISO 8178 E3 cycle

EVERY™
PORT.

Owner

Syarikat Borcos Shipping
Miri, Sarawak, E. Malaysia


Builder

Strategic Marine
Singapore

Cummins Contact

Tim Worme
tim.worme@cummins.com

KTA50



WHY CUMMINS?

Reliable and Durable Products
Excellent Customer Support
Best in Class Life Cycle Cost



Cummins Inc.
4500 Leeds Avenue - Suite 301
Charleston, SC 29405
U.S.A.

E-mail: wavemaster@cummins.com
Internet: <http://marine.cummins.com>

Bulletin M10077 4/06
©2006 Cummins Inc.